




TAPE SELECTOR	BIAS	EQ	RECORDING TIME
NORMAL (IEC TYPE I)	NORMAL	120 $\mu$ s	90min. (2 $\times$ 45)

● **Clear, expansive high-quality sound ... UR**  
Adopts new high-performance, Pure Crystal magnetic particles. Sensitivity has been improved by 0.5 dB in medium and high frequency ranges and MOL is increased by 0.5 dB in the high frequency range. (Compared with our normal-position reference tape 111.)

● **Easy-to-use, high-accuracy cassette**  
Employs see-through, tinted oval-window cassette shell that permits at-a-glance checking of tape running status. Outstanding tape travel performance is also obtained.




0 25215 11161 7

**MAXELL FULL WARRANTY** We warrant to the user of this product that it is free from defective materials and workmanship. If the product proves unsatisfactory, it will be replaced if returned to Maxell America, Inc., 1400 Parker Road, Conyers, Georgia 30207. *Manufacturer, distributor and seller shall not be liable for consequential commercial damages.*

**MAXELL CORPORATION OF AMERICA**  
22-08 ROUTE 208, FAIR LAWN, NJ 07410

Maxell  
MADE IN KOREA



mss180\_b269\_f06