

B

ZAR Inn
Charles Bernstein 3/23/85

N.R. *Dolby* IN OUT

TDK

High Bias

SA90

70µs EQ

MADE IN JAPAN

A

Earl Shen at Ear 3/23/85

N.R. [IN] [OUT]

TDK

High Bias

SA90

70µs EQ

MADE IN JAPAN

MSS. 519

BOX 128

FOLDER 13

POSITION SELECTOR

High(CrO₂)
(TYPE II)

Bias: High
EQ: 70µs

TDK SA 90 (135m) 90min.
@ 1-7/8ips (2 X 45min.)

• TDK Super Avilyn (SA) is ideal for high fidelity recordings. It should be used in the high (CrO₂) position.

wide dynamic range across the frequency spectrum.

-Cassette ist eine Cassette für die High-CrO₂ Position. Durch AVILYN wird den gesamten Frequenzbereich abgedeckt, die die

erfüllte Klangaufzeichnungen ist.

TDK SA est une cassette à jouer en position "High"

mss519_b128_f13